







Abdeckrahmen Gira F300 Schwarz matt (lackiert)



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|------|--------------------|----|---------------|
|  1fach | 0211 84 | 1/10 | 12,60 | 11 | 4010337113508 |
|  2fach | 0212 84 | 1/10 | 19,13 | 11 | 4010337113553 |
|  2fach ohne Mittelsteg | 1002 84 | 1/10 | 19,13 | 11 | 4010337131892 |
|  3fach | 0213 84 | 1/5 | 31,46 | 11 | 4010337113607 |
|  4fach | 0214 84 | 1/5 | 51,10 | 11 | 4010337113652 |
|  5fach | 0215 84 | 1/5 | 77,75 | 11 | 4010337131885 |

Merkmale

- In der Farbvariante Reinweiß glänzend: bestehend aus 85 % biozirkulärem Kunststoff.

Technische Daten

| | |
|-----------------------|---------------------------|
| Abdeckrahmen 1f: | B 80,8 x H 80,8 x T 11,4 |
| Abdeckrahmen 2f: | B 80,8 x H 151,9 x T 11,4 |
| Abdeckrahmen 2f o.M.: | B 80,8 x H 151,9 x T 11,4 |

| | |
|---|---------------------------|
| Abdeckrahmen 3f: | B 80,8 x H 223,4 x T 11,4 |
| Abdeckrahmen 4f: | B 80,8 x H 297,7 x T 11,4 |
| Abdeckrahmen 5f: | B 80,8 x H 366,0 x T 11,4 |
| Eckradius: | R 0,5 |
| Biozirkulärer Kunststoff - Farbvariante Reinweiß glänzend: | min. 50% |
