

## Lautsprecher Unterputz-Radio IP



| Spezifikation                                                                                           | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN           |
|---------------------------------------------------------------------------------------------------------|-------------|----|--------------------|----|---------------|
|  Cremeweiß glänzend    | 2282 01     | 1  | 28,44              | 03 | 4010337076230 |
|  Reinweiß glänzend   | 2282 03     | 1  | 28,44              | 03 | 4010337076247 |
|  Reinweiß seidenmatt | 2282 27     | 1  | 28,44              | 03 | 4010337076254 |
|  Anthrazit           | 2282 28     | 1  | 30,62              | 03 | 4010337076261 |
|  Farbe Alu           | 2282 26     | 1  | 33,36              | 03 | 4010337076162 |
|  Schwarz matt        | 2282 005    | 1  | 33,36              | 03 | 4010337037286 |
|  Grau matt           | 2282 015    | 1  | 33,36              | 03 | 4010337083931 |
|  Edelstahl           | 2282 600    | 1  | 38,28              | 03 | 4010337032861 |

## Merkmale

- Lautsprecher zum Anschluss an das Gira Unterputz-Radio.

---

## Technische Daten

Einbautiefe: 32 mm

Anschlussquerschnitt  
- Lautsprecher-/AUX-Anschluss: 1,5 mm<sup>2</sup>

Impedanz: 8 Ω

Umgebungstemperatur: -5 °C bis +50 °C

---