








## Wipp-Kontrollschalter British Standard (BS EN 60669-1) 20 AX 250 V~mit Wippe Ausschalter 2-polig



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	2834 01	1/10	46,92	29	4010337078814
 Reinweiß glänzend	2834 03	1/10	46,92	29	4010337078821
 Anthrazit	2834 28	1/10	47,43	29	4010337078845
 Farbe Alu	2834 26	1/10	50,54	29	4010337078838
 Schwarz matt	2834 005	1/10	50,54	29	4010337038573
 Grau matt	2834 015	1/10	50,54	29	4010337087137
 Edelstahl	2834 600	1/10	57,72	29	4010337022305

### Technische Daten

Einbautiefe:	24 mm
Anschlussquerschnitt - für Leiter bis:	2 x 4 mm <sup>2</sup> oder 1 x 6 mm <sup>2</sup>

## Hinweise

- Nur für Schraubbefestigung.
  - BS EN 60669-1.
-