

## Abdeckrahmen Gira F100 Reinweiß seidenmatt (lackiert)



| Spezifikation                                                                                             | Bestell-Nr. | VE   | EUR/Stück o. MWSt. | PS | EAN           |
|-----------------------------------------------------------------------------------------------------------|-------------|------|--------------------|----|---------------|
|  1fach                   | 0211 172    | 1/10 | 12,60              | 11 | 4010337133506 |
|  2fach                 | 0212 172    | 1/10 | 19,13              | 11 | 4010337133513 |
|  2fach ohne Mittelsteg | 1002 172    | 1/10 | 19,13              | 11 | 4010337133551 |
|  3fach                 | 0213 172    | 1/5  | 31,46              | 11 | 4010337133520 |
|  4fach                 | 0214 172    | 1/5  | 51,10              | 11 | 4010337133537 |
|  5fach                 | 0215 172    | 1/5  | 77,75              | 11 | 4010337133544 |

### Technische Daten

|                       |                           |
|-----------------------|---------------------------|
| Abdeckrahmen 1f:      | B 83,3 x H 83,3 x T 10,6  |
| Abdeckrahmen 2f:      | B 83,3 x H 154,4 x T 10,6 |
| Abdeckrahmen 2f o.M.: | B 83,3 x H 154,4 x T 10,6 |
| Abdeckrahmen 3f:      | B 83,3 x H 225,9 x T 10,6 |
| Abdeckrahmen 4f:      | B 83,3 x H 297,2 x T 10,6 |
| Abdeckrahmen 5f:      | B 83,3 x H 368,5 x T 10,6 |
| Eckradius:            | R 3                       |

