

## Abdeckrahmen Gira E2 Farbe Alu (lackiert)



| Spezifikation                                                                                             | Bestell-Nr. | VE       | EUR/Stück o. MWSt. | PS | EAN           |
|-----------------------------------------------------------------------------------------------------------|-------------|----------|--------------------|----|---------------|
|  1fach                   | 0211 25     | 1/10/100 | 12,60              | 11 | 4010337211259 |
|  1,5fach               | 1001 25     | 1/10     | 18,64              | 11 | 4010337881346 |
|  2fach                 | 0212 25     | 1/10     | 19,13              | 11 | 4010337212256 |
|  2fach ohne Mittelsteg | 1002 25     | 1/10     | 19,13              | 11 | 4010337002253 |
|  3fach                 | 0213 25     | 1/5      | 31,46              | 11 | 4010337213253 |
|  4fach                 | 0214 25     | 1/5      | 51,10              | 11 | 4010337214250 |
|  5fach                 | 0215 25     | 1/5      | 77,75              | 11 | 4010337215257 |

### Merkmale

- Kunststoff: halogenfreier, schlag- und bruchsicherer Thermoplast

## Hinweise

- Auch für Kanalinstallationen geeignet.
  - Abdeckrahmen (1- bis 5fach) in Verbindung mit Dichtungsset auch für die Montage wassergeschützt Unterputz IP44 geeignet.
-