

## Abdeckrahmen Gira E2 Schwarz matt (lackiert)



| Spezifikation                                                                                             | Bestell-Nr. | VE   | EUR/Stück o. MWSt. | PS | EAN           |
|-----------------------------------------------------------------------------------------------------------|-------------|------|--------------------|----|---------------|
|  1fach                   | 0211 09     | 1/10 | 12,60              | 11 | 4010337036739 |
|  1,5fach               | 1001 09     | 1/10 | 18,64              | 11 | 4010337072775 |
|  2fach                 | 0212 09     | 1/10 | 19,13              | 11 | 4010337036760 |
|  2fach ohne Mittelsteg | 1002 09     | 1/10 | 19,13              | 11 | 4010337036784 |
|  3fach                 | 0213 09     | 1/5  | 31,46              | 11 | 4010337036821 |
|  4fach                 | 0214 09     | 1/5  | 51,10              | 11 | 4010337036869 |
|  5fach                 | 0215 09     | 1/5  | 77,75              | 11 | 4010337036906 |

### Merkmale

- Kunststoff: halogenfreier, schlag- und bruchsicherer Thermoplast

## Hinweise

- Auch für Kanalinstallationen geeignet.
  - Abdeckrahmen (1- bis 5fach) in Verbindung mit Dichtungsset auch für die Montage wassergeschützt Unterputz IP44 geeignet.
-