








Abdeckrahmen Gira E2 Farbe Alu



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|----------|--------------------|----|---------------|
|  1fach | 0211 25 | 1/10/100 | 12,60 | 11 | 4010337211259 |
|  1,5fach | 1001 25 | 1/10 | 18,64 | 11 | 4010337881346 |
|  2fach | 0212 25 | 1/10 | 19,13 | 11 | 4010337212256 |
|  2fach ohne Mittelsteg | 1002 25 | 1/10 | 19,13 | 11 | 4010337002253 |
|  3fach | 0213 25 | 1/5 | 31,46 | 11 | 4010337213253 |
|  4fach | 0214 25 | 1/5 | 51,10 | 11 | 4010337214250 |
|  5fach | 0215 25 | 1/5 | 77,75 | 11 | 4010337215257 |

Merkmale

- Kunststoff: halogenfreier, schlag- und bruchsicherer Thermoplast

Hinweise

- Auch für Kanalinstallationen geeignet.
 - Abdeckrahmen (1- bis 5fach) in Verbindung mit Dichtungsset auch für die Montage wassergeschützt Unterputz IP44 geeignet.
-