









## Steckdose British Standard (BS 1363) 13 A 250 V~ geschaltet, mit Shutter System 55



| Spezifikation  | Bestell-Nr. | VE   | EUR/Stück o. MWSt. | PS | EAN           |
|--|-------------|------|--------------------|----|---------------|
|  Cremeweiß glänzend     | 2778 01     | 1/10 | 21,64              | 29 | 4010337079477 |
|  Reinweiß glänzend    | 2778 03     | 1/10 | 21,64              | 29 | 4010337079484 |
|  Reinweiß seidenmatt  | 2778 27     | 1/10 | 21,64              | 29 | 4010337036418 |
|  Anthrazit            | 2778 28     | 1/10 | 24,35              | 29 | 4010337079507 |
|  Farbe Alu            | 2778 26     | 1/10 | 28,53              | 29 | 4010337079491 |
|  Schwarz matt         | 2778 005    | 1/10 | 28,53              | 29 | 4010337037750 |
|  Grau matt            | 2778 015    | 1/10 | 28,53              | 29 | 4010337086390 |
|  Edelstahl (lackiert) | 2778 600    | 1/10 | 32,42              | 29 | 4010337022091 |

## Merkmale

- Mit Schraubklemmen.
- 

## Technische Daten

Einbautiefe: 20 mm

---

## Hinweise

- Nur für Schraubbefestigung.
  - Weitere Funktionen und Varianten auch für die 80er BS-Dose auf Anfrage erhältlich.
-