

## Wippschalter 3fach 10 AX 250 V~ mit Wippen Universal-Aus-Wechselschalter



| Spezifikation                                                                                            | Bestell-Nr. | VE   | EUR/Stück o. MWSt. | PS | EAN           |
|----------------------------------------------------------------------------------------------------------|-------------|------|--------------------|----|---------------|
|  Cremeweiß glänzend     | 2832 01     | 1/10 | 36,52              | 29 | 4010337832010 |
|  Reinweiß glänzend    | 2832 03     | 1/10 | 36,52              | 29 | 4010337832034 |
|  Anthrazit            | 2832 28     | 1/10 | 39,25              | 29 | 4010337832287 |
|  Farbe Alu            | 2832 26     | 1/10 | 43,42              | 29 | 4010337832263 |
|  Schwarz matt         | 2832 005    | 1/10 | 43,42              | 11 | 4010337038528 |
|  Grau matt            | 2832 015    | 1/10 | 43,42              | 11 | 4010337087120 |
|  Edelstahl (lackiert) | 2832 600    | 1/10 | 47,29              | 29 | 4010337022053 |

### Technische Daten

Einbautiefe: 25 mm

Anschlussquerschnitt  
- für Leiter bis: 2,5 mm<sup>2</sup>

## Hinweise

- Nur für Schraubbefestigung.

---