

Wippschalter 3fach 10 AX 250 V~ mit Wippen Universal-Aus-Wechselschalter



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	2832 01	1/10	36,52	29	4010337832010
 Reinweiß glänzend	2832 03	1/10	36,52	29	4010337832034
 Anthrazit	2832 28	1/10	39,25	29	4010337832287
 Farbe Alu (lackiert)	2832 26	1/10	43,42	29	4010337832263
 Schwarz matt (lackiert)	2832 005	1/10	43,42	11	4010337038528
 Grau matt (lackiert)	2832 015	1/10	43,42	11	4010337087120
 Edelstahl (lackiert)	2832 600	1/10	47,29	29	4010337022053

Technische Daten

Einbautiefe:	25 mm
Anschlussquerschnitt - für Leiter bis:	2,5 mm ²

Hinweise

- Nur für Schraubbefestigung.
