









## Wippschalter British Standard (BS EN 60669-1) 20 AX 250 V~ mit Wippe Ausschalter 2-polig



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	2836 01	1/10	38,99	29	4010337078944
 Reinweiß glänzend	2836 03	1/10	38,99	29	4010337078951
 Anthrazit	2836 28	1/10	39,71	29	4010337078975
 Farbe Alu	2836 26	1/10	42,87	29	4010337078968
 Schwarz matt	2836 005	1/10	42,87	29	4010337038566
 Grau matt	2836 015	1/10	42,87	29	4010337087144
 Edelstahl	2836 600	1/10	49,81	29	4010337021933

### Technische Daten

Einbautiefe:	24 mm
Anschlussquerschnitt - für Leiter bis:	2 x 4 mm <sup>2</sup> oder 1 x 6 mm <sup>2</sup>

## Hinweise

- Nur für Schraubbefestigung.
  - BS EN 60669-1.
-