







Steckdose mit Schutzkontakt EURO-US 16 A 250 V~



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	2840 01	1/10	15,44	29	4010337840015
 Reinweiß glänzend	2840 03	1/10	15,44	29	4010337840039
 Reinweiß seidenmatt	2840 27	1/10	15,44	29	4010337840275
 Anthrazit	2840 28	1/10	16,78	29	4010337840282
 Farbe Alu	2840 26	1/10	21,73	29	4010337840268
Schwarz matt	2840 005	1/10	21,73	11	4010337037873
 Edelstahl (lackiert)	2840 600	1/10	25,65	11	4010337022213

Technische Daten

Einbautiefe: 20 mm