






## System 3000 Bedieneinsatz 2fach System 70



| Spezifikation  | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|--|-------------|-----|--------------------|----|---------------|
|  Reinweiß glänzend                | 5362 70     | 1/5 | 46,74              | 02 | 4010337118107 |
|  Reinweiß seidenmatt (lackiert) | 5362 72     | 1/5 | 54,47              | 02 | 4010337118114 |
|  Anthrazit (lackiert)           | 5362 73     | 1/5 | 54,47              | 02 | 4010337118084 |
|  Schwarz matt (lackiert)        | 5362 74     | 1/5 | 54,47              | 02 | 4010337118121 |
|  Grau matt (lackiert)           | 5362 76     | 1/5 | 54,47              | 02 | 4010337118091 |

### Technische Daten

Umgebungstemperatur: -20 °C bis +45 °C