













## Wippe für Wippenet 4fach für Tastsensor 4.95



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Aluminium Reinweiß glänzend (lackiert)	8334 903	1	45,10	06	4010337098720
 Aluminium Reinweiß seidenmatt (lackiert)	8334 927	1	45,10	06	4010337098744
 Aluminium Anthrazit (lackiert)	8334 928	1	45,10	06	4010337098683
 Aluminium (eloxiert)	8334 17	1	33,08	06	4010337096986
 Aluminium Schwarz matt (lackiert)	8334 905	1	45,10	06	4010337098706
 Aluminium Grau matt (lackiert)	8334 915	1	45,10	06	4010337098669
 Aluminium Schwarz (eloxiert)	8334 126	1	33,08	06	4010337097228
 Bronze (PVD)	8334 38	1	78,18	06	4010337098775
 Glas Weiß	8334 12	1	33,08	06	4010337098010

---

 Glas Schwarz	8334 05	1	33,08	06	4010337098034
<hr/>					
 Edelstahl	8334 219	1	60,13	06	4010337097785
<hr/>					