© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Circuit breaker, 2-pole



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 grey	0112 31	-	-	-	4010337112310

Features

- With neon lamp element.
- Water-protected surface-mounted IP66

Technical data

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Rated output
- LEDi/CFLi: 100 W

Notes

- Subject to availability.
- Can also be connected to be illuminated.

Scope of supply

- Blank inscription label enclosed.
- Inscription label "Heating On/Off", "VERWARMING AAN/UIT" is enclosed.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.