




Button 10 A 250 V~ with upright rocker with control window 2-way momentary contact, 1-pole



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white	0120 66	-	-	-	4010337120667
 anthracite	0120 67	-	-	-	4010337120674
 colour aluminium	0120 65	-	-	-	4010337120650

Technische Daten

Installation depth:	28 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm ²

Hinweise

- With touch-activation operation.
- Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.
- Vertical rocker position matches the pushbutton switches.
- Can also be connected to be illuminated.
- Subject to availability.