© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Pushbutton switch 10 AX 250 V~ with rocker, 2-gang Series switch



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
pure white	0125 66	-	-	-	4010337125662
anthracite (lacquered)	0125 67	-	-	-	4010337125679
colour aluminium (lacquered)	0125 65	-	-	-	4010337125655

Technical data

Installation depth
- 0125 ..: 25 mm
- 0128 ..: 28 mm

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Rated output
- LEDi/CFLi: 100 W

Notes

- With touch-activation operation.
- Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.
- Subject to availability.
- Successor item: 3125 00 + 3495 xxAvailable from 08/2024.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.