




Pushbutton switch 10 AX 250 V~ with rocker, 2-gang Series switch



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white	0125 66	-	-	-	4010337125662
 anthracite	0125 67	-	-	-	4010337125679
 colour aluminium	0125 65	-	-	-	4010337125655

Technische Daten

Installation depth

- 0125 ...:	25 mm
- 0128 ...:	28 mm

Connection cross section

- For rigid and flexible conductors up to:	2.5 mm ²
--	---------------------

Rated output

- LEDi/CFLi:	100 W
--------------	-------

Hinweise

- With touch-activation operation.
- Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.
- Subject to availability.
- Successor item: 3125 00 + 3495 xx Available from 08/2024.