




Pushbutton switch 10 AX 250 V~ with rocker, 2-gang 2-way switch, 2-gang



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white	0128 66	-	-	-	4010337128663
 anthracite	0128 67	-	-	-	4010337128670
 colour aluminium	0128 65	-	-	-	4010337128656

Technische Daten

Installation depth	
- 0125 ...:	25 mm
- 0128 ...:	28 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm ²
Rated output	
- LEDi/CFLi:	100 W

Hinweise

- With touch-activation operation.
- Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.
- Subject to availability.
- Successor item: 3128 00 + 3495 xx Available from 08/2024.