




Button 10 A 250 V~ with upright rocker 2-way momentary contact, 1-pole



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white	0130 66	-	-	-	4010337130666
 anthracite	0130 67	-	-	-	4010337130673
 colour aluminium	0130 65	-	-	-	4010337130659

Technische Daten

Installation depth:	28 mm
Connection cross section - For rigid and flexible conductors up to:	2.5 mm ²

Hinweise

- With touch-activation operation.
- Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.
- Vertical rocker position matches the pushbutton switches.
- Subject to availability.