

Short-stroke button 0.5 A 42 V~ with rocker NO contact, 1-pole



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	0138 01	-	-	-	4010337138013
 pure white glossy	0138 03	-	-	-	4010337138037
 pure white matt	0138 27	-	-	-	4010337138273
 anthracite	0138 28	-	-	-	4010337138280
 colour aluminium	0138 26	-	-	-	4010337138266
 black matt	0138 005	-	-	-	4010337037262

Merkmale

- With screw terminals.

Technische Daten

Installation depth: 11 mm

Hinweise

- For terminal and dowel mounting.
