






Rocker button insert 10 A 250 V~



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 NO contact, 1-pole	0151 00	-	-	-	4010337151005
 2-way momentary contact, 1-pole	0156 00	-	-	-	4010337156000
 1-pole NO contact with N terminal	0150 00	-	-	-	4010337150008
 1-pole NO contact with sep. signal contact	0152 00	-	-	-	4010337152002

Technische Daten

Installation depth:	32 mm
Connection cross section - For rigid and flexible conductors up to:	2.5 mm ²

Hinweise

- Can also be connected to be illuminated.
- Subject to availability.