







## Gira Standard 55 cover frame cream white glossy



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	0211 01	1/10/100	2.89	21	4010337211013
 2-gang	0212 01	1/10/100	4.93	21	4010337212010
 2-gang, without crossbar	1002 01	1/10	3.65	01	4010337002017
 3-gang	0213 01	1/10/100	8.69	01	4010337213017
 4-gang	0214 01	1/5	15.04	01	4010337214014
 5-gang	0215 01	1/5	24.74	01	4010337215011

### Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.

### Hinweise

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.