







## Gira F100 cover frame pure white glossy



| Spezifikation  | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN           |
|--|-------------|----|--------------------|----|---------------|
|  1-gang                     | 0211 112    | -  | -                  | -  | 4010337043973 |
|  2-gang                   | 0212 112    | -  | -                  | -  | 4010337044017 |
|  2-gang, without crossbar | 1002 112    | -  | -                  | -  | 4010337047094 |
|  3-gang                   | 0213 112    | -  | -                  | -  | 4010337044031 |
|  4-gang                   | 0214 112    | -  | -                  | -  | 4010337044055 |
|  5-gang                   | 0215 112    | -  | -                  | -  | 4010337044079 |

### Merkmale

- Shatter-proof.
- In the Pure White Gloss finish: made from 85% bio-based plastic.

### Technische Daten

|                         |                           |
|-------------------------|---------------------------|
| Cover frame 1-g:        | B 83,3 x H 83,3 x T 10,6  |
| Cover frame 2-g:        | B 83,3 x H 154,4 x T 10,6 |
| Cover frame 2-g w/o cb: | B 83,3 x H 154,4 x T 10,6 |

|                                     |                           |
|-------------------------------------|---------------------------|
| Cover frame 3-g:                    | B 83,3 x H 225,9 x T 10,6 |
| Cover frame 4-g:                    | B 83,3 x H 297,2 x T 10,6 |
| Cover frame 5-g:                    | B 83,3 x H 368,5 x T 10,6 |
| Corner radius:                      | R 3                       |
| Biocircular plastic                 |                           |
| - Colour option: Pure white glossy: | at least 50%              |

---

## Hinweise

- In combination with a sealing flange, also suitable for mounting as water-protected flush-mounted IP44.

---