







Gira F200 cover frame grey matt (lacquered)



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|--|-------------|------|--------------------|----|---------------|
|  1-gang | 0211 76 | 1/10 | 11.37 | 11 | 4010337113164 |
|  2-gang | 0212 76 | 1/10 | 20.01 | 11 | 4010337113218 |
|  2-gang, without crossbar | 1002 76 | 1/10 | 20.01 | 11 | 4010337113423 |
|  3-gang | 0213 76 | 1/5 | 30.80 | 11 | 4010337113263 |
|  4-gang | 0214 76 | 1/5 | 49.89 | 11 | 4010337113324 |
|  5-gang | 0215 76 | 1/5 | 75.97 | 11 | 4010337113379 |

Merkmale

- In the Pure White Gloss finish: made from 85% bio-based plastic.

Technische Daten

| | |
|-------------------------|---------------------------|
| Cover frame 1-g: | B 90,0 x H 90,0 x T 11,4 |
| Cover frame 2-g: | B 90,0 x H 161,1 x T 11,4 |
| Cover frame 2-g w/o cb: | B 90,0 x H 161,1 x T 11,4 |

GIRA Parts list

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

| | |
|--|---------------------------|
| Cover frame 3-g: | B 90,0 x H 232,6 x T 11,4 |
| Cover frame 4-g: | B 90,0 x H 303,9 x T 11,4 |
| Cover frame 5-g: | B 90,0 x H 375,2 x T 11,4 |
| Corner radius: | R 0.3 |
| Biocircular plastic - Colour option: Pure white glossy: | at least 50% |
