

## Gira F100 cover frame pure white matt (lacquered)



| Specification                                                                                                | Order No. | Packing unit | GBP/piece<br>without VAT | PS | EAN           |
|--------------------------------------------------------------------------------------------------------------|-----------|--------------|--------------------------|----|---------------|
|  1-gang                    | 0211 172  | 1/10         | 11.34                    | 11 | 4010337133506 |
|  2-gang                   | 0212 172  | 1/10         | 17.22                    | 11 | 4010337133513 |
|  2-gang, without crossbar | 1002 172  | 1/10         | 17.22                    | 11 | 4010337133551 |
|  3-gang                   | 0213 172  | 1/5          | 28.31                    | 11 | 4010337133520 |
|  4-gang                   | 0214 172  | 1/5          | 45.99                    | 11 | 4010337133537 |
|  5-gang                   | 0215 172  | 1/5          | 69.98                    | 11 | 4010337133544 |

### Technical data

|                         |                           |
|-------------------------|---------------------------|
| Cover frame 1-g:        | B 83,3 x H 83,3 x T 10,6  |
| Cover frame 2-g:        | B 83,3 x H 154,4 x T 10,6 |
| Cover frame 2-g w/o cb: | B 83,3 x H 154,4 x T 10,6 |
| Cover frame 3-g:        | B 83,3 x H 225,9 x T 10,6 |
| Cover frame 4-g:        | B 83,3 x H 297,2 x T 10,6 |
| Cover frame 5-g:        | B 83,3 x H 368,5 x T 10,6 |

Corner radius:

R 3

---