







Gira E2 cover frame pure white glossy



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|--|-------------|----------|--------------------|----|---------------|
|  1-gang | 0211 29 | 1/10/100 | 6.99 | 01 | 4010337211297 |
|  2-gang | 0212 29 | 1/10/100 | 9.60 | 01 | 4010337212294 |
|  2-gang, without crossbar | 1002 29 | 1/10 | 9.60 | 01 | 4010337001553 |
|  3-gang | 0213 29 | 1/5 | 17.52 | 01 | 4010337213291 |
|  4-gang | 0214 29 | 1/5 | 28.31 | 01 | 4010337214298 |
|  5-gang | 0215 29 | 1/5 | 43.19 | 01 | 4010337215295 |

Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.

Hinweise

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.