# **GIRA** Data sheet



© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

**Gira E2 cover frame pure white matt**



| Specification | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|
|  1-gang | 0211 22 | 1/10/100 | 6.99 | 01 | 4010337211228 |
|  1.5-gang | 1001 22 | - | - | - | 4010337881322 |
|  2-gang | 0212 22 | 1/10/100 | 9.60 | 01 | 4010337212225 |
|  2-gang, without crossbar | 1002 22 | 1/10 | 9.60 | 01 | 4010337002222 |
|  3-gang | 0213 22 | 1/5 | 17.52 | 01 | 4010337213222 |
|  4-gang | 0214 22 | 1/5 | 28.31 | 01 | 4010337214229 |
|  5-gang | 0215 22 | 1/5 | 43.19 | 01 | 4010337215226 |

**Features**

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic” or would that then be polycarbonate.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Notes**

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.

---