

Gira F200 cover frame pure white glossy



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	0211 70	1/10	7.02	01	4010337113171
 2-gang	0212 70	1/10	12.39	01	4010337113225
 2-gang, without crossbar	1002 70	1/10	12.39	01	4010337113430
 3-gang	0213 70	1/5	20.01	01	4010337113270
 4-gang	0214 70	1/5	32.20	01	4010337113331
 5-gang	0215 70	1/5	49.19	01	4010337113386

Technische Daten

Cover frame 1-g:	B 90,0 x H 90,0 x T 11,4
Cover frame 2-g:	B 90,0 x H 161,1 x T 11,4
Cover frame 2-g w/o cb:	B 90,0 x H 161,1 x T 11,4
Cover frame 3-g:	B 90,0 x H 232,6 x T 11,4
Cover frame 4-g:	B 90,0 x H 303,9 x T 11,4
Cover frame 5-g:	B 90,0 x H 375,2 x T 11,4
Corner radius:	R 0.3

Biocircular plastic
- Colour option: Pure white glossy: at least 50%
