© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Gira F100 cover frame pure white glossy

Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
1-gang	0211 112	-	-	-	4010337043973
2-gang	0212 112	-	-	-	4010337044017
2-gang, without crossbar	1002 112	-	-	-	4010337047094
3-gang	0213 112	-	-	-	4010337044031
4-gang	0214 112	-	-	-	4010337044055
5-gang	0215 112	-	-	-	4010337044079

Features

- Shatter-proof.
- In the pure white glossy colour variant: consisting of 85% biocircular plastic.

Technical data

Cover frame 1-g:	B 83,3 x H 83,3 x T 10,6
Cover frame 2-g:	B 83,3 x H 154,4 x T 10,6

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Cover frame 2-g w/o cb:	B 83,3 x H 154,4 x T 10,6
Cover frame 3-g:	B 83,3 x H 225,9 x T 10,6
Cover frame 4-g:	B 83,3 x H 297,2 x T 10,6
Cover frame 5-g:	B 83,3 x H 368,5 x T 10,6
Corner radius:	R 3
Biocircular plastic - Colour option: Pure white glossy:	at least 50%

Notes

- In combination with a sealing flange, also suitable for mounting as water-protected flush-mounted IP44.
