






Gira E1 cover frame anthracite



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|--------------------------------------------------------------------------------------------------------------|-------------|------|--------------------|----|---------------|
|  1-gang | 0211 152 | 1/10 | 7.34 | 11 | 4010337125969 |
|  2-gang | 0212 152 | 1/10 | 10.61 | 11 | 4010337125976 |
|  2-gang, without crossbar | 1002 152 | 1 | 10.61 | 11 | 4010337125983 |
|  3-gang | 0213 152 | 1/5 | 18.38 | 11 | 4010337125990 |
|  4-gang | 0214 152 | 1/5 | 29.60 | 11 | 4010337126027 |
|  5-gang | 0215 152 | 1/5 | 45.14 | 11 | 4010337126041 |

Merkmale

- Shatter-proof.

Hinweise

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.