

Gira F300 cover frame pure white glossy



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	0211 80	1/10	6.99	01	4010337113478
 2-gang	0212 80	1/10	9.60	01	4010337113539
 2-gang, without crossbar	1002 80	1/10	9.60	01	4010337131830
 3-gang	0213 80	1/5	17.52	01	4010337113584
 4-gang	0214 80	1/5	28.31	01	4010337113638
 5-gang	0215 80	1/5	43.19	01	4010337131823

Merkmale

- In the Pure White Gloss finish: made from 85% bio-based plastic.

Technische Daten

Cover frame 1-g:	B 80,8 x H 80,8 x T 11,4
Cover frame 2-g:	B 80,8 x H 151,9 x T 11,4
Cover frame 2-g w/o cb:	B 80,8 x H 151,9 x T 11,4

Cover frame 3-g: B 80,8 x H 223,4 x T 11,4

Cover frame 4-g: B 80,8 x H 297,7 x T 11,4

Cover frame 5-g: B 80,8 x H 366,0 x T 11,4

Corner radius: R 0.5

Biocircular plastic

- Colour option: Pure white glossy: at least 50%
