

Gira F300 cover frame pure white matt (lacquered)



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	0211 82	1/10	11.34	11	4010337113485
 2-gang	0212 82	1/10	17.22	11	4010337113546
 2-gang, without crossbar	1002 82	1/10	17.22	11	4010337131854
 3-gang	0213 82	1/5	28.31	11	4010337113591
 4-gang	0214 82	1/5	45.99	11	4010337113645
 5-gang	0215 82	1/5	69.98	11	4010337131847

Merkmale

- In the Pure White Gloss finish: made from 85% bio-based plastic.

Technische Daten

Cover frame 1-g:	B 80,8 x H 80,8 x T 11,4
Cover frame 2-g:	B 80,8 x H 151,9 x T 11,4
Cover frame 2-g w/o cb:	B 80,8 x H 151,9 x T 11,4

Cover frame 3-g: B 80,8 x H 223,4 x T 11,4

Cover frame 4-g: B 80,8 x H 297,7 x T 11,4

Cover frame 5-g: B 80,8 x H 366,0 x T 11,4

Corner radius: R 0.5

Biocircular plastic

- Colour option: Pure white glossy: at least 50%
