








Gira E2 cover frame black matt



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	0211 09	1/10	11.34	11	4010337036739
 1.5-gang	1001 09	1/10	16.78	11	4010337072775
 2-gang	0212 09	1/10	17.22	11	4010337036760
 2-gang, without crossbar	1002 09	1/10	17.22	11	4010337036784
 3-gang	0213 09	1/5	28.31	11	4010337036821
 4-gang	0214 09	1/5	45.99	11	4010337036869
 5-gang	0215 09	1/5	69.98	11	4010337036906

Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.

Hinweise

- Also suitable for duct installation.
 - In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.
-