







Gira F100 cover frame anthracite (lacquered)



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|--|-------------|------|--------------------|----|---------------|
|  1-gang | 0211 173 | 1/10 | 11.34 | 11 | 4010337135951 |
|  2-gang | 0212 173 | 1/10 | 17.22 | 11 | 4010337133568 |
|  2-gang, without crossbar | 1002 173 | 1/10 | 17.22 | 11 | 4010337133605 |
|  3-gang | 0213 173 | 1/5 | 28.31 | 11 | 4010337133575 |
|  4-gang | 0214 173 | 1/5 | 45.99 | 11 | 4010337133582 |
|  5-gang | 0215 173 | 1/5 | 69.98 | 11 | 4010337133599 |

Merkmale

- In the Pure White Gloss finish: made from 85% bio-based plastic.

Technische Daten

| | |
|-------------------------|---------------------------|
| Cover frame 1-g: | B 83,3 x H 83,3 x T 10,6 |
| Cover frame 2-g: | B 83,3 x H 154,4 x T 10,6 |
| Cover frame 2-g w/o cb: | B 83,3 x H 154,4 x T 10,6 |

GIRA Parts list

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Cover frame 3-g: B 83,3 x H 225,9 x T 10,6

Cover frame 4-g: B 83,3 x H 297,2 x T 10,6

Cover frame 5-g: B 83,3 x H 368,5 x T 10,6

Corner radius: R 3

Biocircular plastic

- Colour option: Pure white glossy: at least 50%
