






## Gira F100 cover frame black matt (lacquered)



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	0211 174	1/10	11.34	11	4010337135968
 2-gang	0212 174	1/10	17.22	11	4010337133612
 2-gang, without crossbar	1002 174	1/10	17.22	11	4010337133650
 3-gang	0213 174	1/5	28.31	11	4010337133629
 4-gang	0214 174	1/5	45.99	11	4010337133636
 5-gang	0215 174	1/5	69.98	11	4010337135845

### Merkmale

- In the Pure White Gloss finish: made from 85% bio-based plastic.

### Technische Daten

Cover frame 1-g:	B 83,3 x H 83,3 x T 10,6
Cover frame 2-g:	B 83,3 x H 154,4 x T 10,6
Cover frame 2-g w/o cb:	B 83,3 x H 154,4 x T 10,6

# GIRA Parts list

catalogue.gira.com

© Copyright by  
Gira Giersiepen GmbH & Co. KG  
All rights reserved

www.gira.com

Cover frame 3-g:	B 83,3 x H 225,9 x T 10,6
Cover frame 4-g:	B 83,3 x H 297,2 x T 10,6
Cover frame 5-g:	B 83,3 x H 368,5 x T 10,6
Corner radius:	R 3
Biocircular plastic - Colour option: Pure white glossy:	at least 50%

---