







## Gira F100 cover frame grey matt (lacquered)



| Spezifikation  | Bestell-Nr. | VE   | GBP/Stück o. MWSt. | PS | EAN           |
|--|-------------|------|--------------------|----|---------------|
|  1-gang                     | 0211 176    | 1/10 | 11.34              | 11 | 4010337136026 |
|  2-gang                   | 0212 176    | 1/10 | 17.22              | 11 | 4010337133667 |
|  2-gang, without crossbar | 1002 176    | 1/10 | 17.22              | 11 | 4010337133704 |
|  3-gang                   | 0213 176    | 1/5  | 28.31              | 11 | 4010337133674 |
|  4-gang                   | 0214 176    | 1/5  | 45.99              | 11 | 4010337133681 |
|  5-gang                   | 0215 176    | 1/5  | 69.98              | 11 | 4010337135852 |

### Merkmale

- In the Pure White Gloss finish: made from 85% bio-based plastic.

### Technische Daten

|                         |                           |
|-------------------------|---------------------------|
| Cover frame 1-g:        | B 83,3 x H 83,3 x T 10,6  |
| Cover frame 2-g:        | B 83,3 x H 154,4 x T 10,6 |
| Cover frame 2-g w/o cb: | B 83,3 x H 154,4 x T 10,6 |

# GIRA Parts list

catalogue.gira.com

© Copyright by  
Gira Giersiepen GmbH & Co. KG  
All rights reserved

www.gira.com

|  |                           |
|--|---------------------------|
| Cover frame 3-g:   | B 83,3 x H 225,9 x T 10,6 |
| Cover frame 4-g:   | B 83,3 x H 297,2 x T 10,6 |
| Cover frame 5-g:   | B 83,3 x H 368,5 x T 10,6 |
| Corner radius:   | R 3                       |
| Biocircular plastic<br>- Colour option: Pure white glossy: | at least 50%              |

---