







Gira E2 cover frame pure white glossy



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	0211 29	1/10/100	6.99	01	4010337211297
 2-gang	0212 29	1/10/100	9.60	01	4010337212294
 2-gang, without crossbar	1002 29	1/10	9.60	01	4010337001553
 3-gang	0213 29	1/5	17.52	01	4010337213291
 4-gang	0214 29	1/5	28.31	01	4010337214298
 5-gang	0215 29	1/5	43.19	01	4010337215295

Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.

Hinweise

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.