








Gira E2 cover frame



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	0211 33	1/10	17.87	11	4010337019794
 2-gang	0212 33	1/10	27.70	11	4010337019800
 2-gang, without crossbar	1002 33	1/10	27.70	11	4010337019848
 3-gang	0213 33	1/5	50.92	11	4010337019817
 4-gang	0214 33	1/5	79.02	11	4010337019824
 5-gang	0215 33	1/5	120.35	11	4010337019831

Hinweise

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.