






Gira F300 cover frame anthracite (lacquered)



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|--|-------------|------|--------------------|----|---------------|
|  1-gang | 0211 83 | 1/10 | 11.34 | 11 | 4010337113461 |
|  2-gang | 0212 83 | 1/10 | 17.22 | 11 | 4010337113515 |
|  2-gang, without crossbar | 1002 83 | 1/10 | 17.22 | 11 | 4010337131878 |
|  3-gang | 0213 83 | 1/5 | 28.31 | 11 | 4010337113560 |
|  4-gang | 0214 83 | 1/5 | 45.99 | 11 | 4010337113614 |
|  5-gang | 0215 83 | 1/5 | 69.98 | 11 | 4010337131861 |

Merkmale

- In the Pure White Gloss finish: made from 85% bio-based plastic.

Technische Daten

| | |
|-------------------------|---------------------------|
| Cover frame 1-g: | B 80,8 x H 80,8 x T 11,4 |
| Cover frame 2-g: | B 80,8 x H 151,9 x T 11,4 |
| Cover frame 2-g w/o cb: | B 80,8 x H 151,9 x T 11,4 |

GIRA Parts list

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

| | |
|--|---------------------------|
| Cover frame 3-g: | B 80,8 x H 223,4 x T 11,4 |
| Cover frame 4-g: | B 80,8 x H 297,7 x T 11,4 |
| Cover frame 5-g: | B 80,8 x H 366,0 x T 11,4 |
| Corner radius: | R 0.5 |
| Biocircular plastic - Colour option: Pure white glossy: | at least 50% |
