© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Electronic potentiometer insert for 1 – 10 V control input Switching function



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
	0309 00	1/5	50.75	02	4010337309000

Features

- Electronic potentiometer with switching function for electronic ballasts or Tronic transformers with 1 – 10 V control input.
- Pressing the operating button switches the electronic ballasts on and off.
- Rotating adjusts the brightness.
- Basic brightness can be set.
- Short-circuit protection of the switching contact by integrated fine fuse.

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
1 – 10 V interface	
- Control voltage:	0.7 to 12 V
- Control current:	max. 50 mA
Switching current	
- Ohmic:	6 A
Installation depth:	32 mm
Ambient temperature:	+5 °C to +25 °C

Scope of supply

- Fuse is included with delivery.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.