







Stereo speaker socket outlet



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	0402 01	1/5	18.04	01	4010337402015
 pure white glossy	0402 03	1/5	18.04	01	4010337402039
 pure white matt	0402 27	1/5	18.04	01	4010337402275
 anthracite	0402 28	1/5	20.55	11	4010337402282
 colour aluminium	0402 26	1/5	23.10	11	4010337402268
 black matt	0402 005	1/5	23.10	11	4010337037880

Merkmale

- With screw terminals.

Technische Daten

Installation depth: 31 mm
 Connection cross section, max.: 1.5 mm²

Hinweise

- For cable cross section up to max. 10 mm².
