


## Equipotential bonding socket, 2-gang System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	0405 01	1/5	37.79	01	4010337405016
 pure white glossy	0405 03	1/5	37.79	01	4010337405030
 pure white matt	0405 27	1/5	37.79	01	4010337405276
 anthracite	0405 28	1/5	40.29	11	4010337405283
 colour aluminium	0405 26	1/5	44.22	11	4010337405269
 black matt	0405 005	1/5	44.22	11	4010337037316

### Merkmale

- For the connection of medical devices. DIN 42 801.

### Technische Daten

Installation depth: 31 mm  
Connection cross section: 6 bis 10 mm<sup>2</sup>