









## Cover for coaxial antenna socket



| Spezifikation   | Bestell-Nr. | VE       | GBP/Stück o. MWSt. | PS | EAN           |
|---|-------------|----------|--------------------|----|---------------|
|  cream white glossy  | 0869 01     | 1/10/100 | 6.06               | 01 | 4010337869016 |
|  pure white glossy | 0869 03     | 1/10/100 | 6.06               | 01 | 4010337009504 |
|  pure white matt   | 0869 27     | 1/10/100 | 6.06               | 01 | 4010337869276 |
|  anthracite        | 0869 28     | 1/10     | 8.61               | 11 | 4010337869283 |
|  colour aluminium  | 0869 26     | 1/10     | 12.52              | 11 | 4010337869269 |
|  black matt        | 0869 005    | 1/10     | 12.52              | 11 | 4010337036616 |
|  grey matt         | 0869 015    | 1/10     | 12.52              | 11 | 4010337081890 |
|  stainless steel   | 0869 600    | 1/5      | 16.23              | 11 | 4010337021605 |

## **Merkmale**

- Third hole can be broken out.
-