








## Gira E2 cover frame pure white matt



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	0211 22	1/10/100	6.99	01	4010337211228
 1.5-gang	1001 22	-	-	-	4010337881322
 2-gang	0212 22	1/10/100	9.60	01	4010337212225
 2-gang, without crossbar	1002 22	1/10	9.60	01	4010337002222
 3-gang	0213 22	1/5	17.52	01	4010337213222
 4-gang	0214 22	1/5	28.31	01	4010337214229
 5-gang	0215 22	1/5	43.19	01	4010337215226

### Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.

## Hinweise

- Also suitable for duct installation.
  - In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.
-