






## Cover frame pure white glossy



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 1-gang	0211 112	-	-	-	4010337043973
 2-gang	0212 112	-	-	-	4010337044017
 2-gang, without crossbar	1002 112	-	-	-	4010337047094
 3-gang	0213 112	-	-	-	4010337044031
 4-gang	0214 112	-	-	-	4010337044055
 5-gang	0215 112	-	-	-	4010337044079

### Merkmale

- Shatter-proof.
- In the Pure White Gloss finish: made from 85% bio-based plastic.

### Technische Daten

Cover frame 1-g:	B 83,3 x H 83,3 x T 10,6
Cover frame 2-g:	B 83,3 x H 154,4 x T 10,6
Cover frame 2-g w/o cb:	B 83,3 x H 154,4 x T 10,6

Cover frame 3-g:	B 83,3 x H 225,9 x T 10,6
Cover frame 4-g:	B 83,3 x H 297,2 x T 10,6
Cover frame 5-g:	B 83,3 x H 368,5 x T 10,6
Corner radius:	R 3
Biocircular plastic	
- Colour option: Pure white glossy:	at least 50%

---

## Hinweise

- In combination with a sealing flange, also suitable for mounting as water-protected flush-mounted IP44.

---