

## Gira E1 cover frame anthracite



| Spezifikation                                                                                                | Bestell-Nr. | VE   | GBP/Stück o. MWSt. | PS | EAN           |
|--------------------------------------------------------------------------------------------------------------|-------------|------|--------------------|----|---------------|
|  1-gang                     | 0211 152    | 1/10 | 7.34               | 11 | 4010337125969 |
|  2-gang                   | 0212 152    | 1/10 | 10.61              | 11 | 4010337125976 |
|  2-gang, without crossbar | 1002 152    | 1    | 10.61              | 11 | 4010337125983 |
|  3-gang                   | 0213 152    | 1/5  | 18.38              | 11 | 4010337125990 |
|  4-gang                   | 0214 152    | 1/5  | 29.60              | 11 | 4010337126027 |
|  5-gang                   | 0215 152    | 1/5  | 45.14              | 11 | 4010337126041 |

### Merkmale

- Shatter-proof.

### Hinweise

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.