






## Gira E2 cover frame for flat installation pure white glossy



| Spezifikation  | Bestell-Nr. | VE   | GBP/Stück o. MWSSt. | PS | EAN           |
|--|-------------|------|---------------------|----|---------------|
|  1-gang                     | 0211 295    | 1/10 | 8.27                | 01 | 4010337022299 |
|  2-gang                   | 0212 295    | 1/10 | 13.29               | 01 | 4010337022282 |
|  2-gang, without crossbar | 1002 295    | 1/10 | 13.29               | 01 | 4010337022251 |
|  3-gang                   | 0213 295    | 1/5  | 21.91               | 01 | 4010337022275 |
|  4-gang                   | 0214 295    | 1/5  | 34.74               | 01 | 4010337022268 |

### Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.