








Gira E2 cover frame grey matt



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|--|-------------|------|--------------------|----|---------------|
|  1-gang | 0211 37 | 1/10 | 11.34 | 11 | 4010337077299 |
|  1.5-gang | 1001 37 | 1/10 | 16.78 | 11 | 4010337082422 |
|  2-gang | 0212 37 | 1/10 | 17.22 | 11 | 4010337077589 |
|  2-gang, without crossbar | 1002 37 | 1/10 | 17.22 | 11 | 4010337082439 |
|  3-gang | 0213 37 | 1/5 | 28.31 | 11 | 4010337077602 |
|  4-gang | 0214 37 | 1/5 | 45.99 | 11 | 4010337077626 |
|  5-gang | 0215 37 | 1/5 | 69.98 | 11 | 4010337077640 |

Merkmale

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.

Hinweise

- Also suitable for duct installation.
 - In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.
-