




Surface-mounted housing, including cover frame black matt



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|--|-------------|----|--------------------|----|---------------|
|  1-gang | 1061 74 | 1 | 37.97 | 13 | 4010337109440 |
|  2-gang | 1062 74 | 1 | 60.37 | 13 | 4010337109457 |
|  3-gang | 1063 74 | 1 | 81.94 | 13 | 4010337109464 |

Technische Daten

| | |
|------------------|---------------------------|
| Cover frame 1-g: | B 89,9 x H 89,9 x T 53,3 |
| Cover frame 2-g: | B 89,9 x H 161,0 x T 53,3 |
| Cover frame 3-g: | B 89,9 x H 232,5 x T 53,3 |
| Corner radius: | R 0.3 |